
Operating Instruction (ST-3)

Features

Fashionable appearance, small and exquisite; powerful cupule adsorbable to any slick plane, especially for aquarium, refrigerator etc...

Technical parameter

- Temperature range: $-50^{\circ}\text{C} \sim +70^{\circ}\text{C}$
- Accuracy : $\pm 1^{\circ}\text{C}$
- Usage temperature: $-10^{\circ}\text{C} \sim +50^{\circ}\text{C}$
- Distinguish rate: 0.1°C
- Power: button battery (DC1.5V)

Operation description

- Open the battery cover, put in one LR44 battery correctly, be assure not turn over;
- Display once put in the battery. Press [FSW] for 3 seconds to power off or take out the battery when no use for long time (Press [FSW] for on/off);
- LCD display H°C when temperature higher than 70°C , LCD display L°C when temperature lower than -50°C .